



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D <i>* : Required Field</i>

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2018-10-24
Company Unique ID	NL 008751171B01		
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Contact Phone *	Refer to Supplier Comment section	Contact Email *	Refer to Supplier Comment section
Authorized Representative *	Floriana SAN BIAGIO	Representative Title	AMS MD CHAMPION
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement		
Supplier Acceptance *	true	Legal Declaration *
		Standard

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
	Mfr Item Name	Version	Mfr Site	Date
	CDO7*3702AAW	A	BO2A	2018-10-24
	Amount	UoM	Unit type	ST ECOPACK Grade
	80	mg	Each	ECOPACK® 3
Comment	ECOPACK® 3 is STMicroelectronics trade name for ROHS compliant device without use of any ROHS exemption and without Halogen nor Antimony			

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
1	260	3		
Bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
Not Applicable	Tin (Sn), matte, annealed	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
DSO	4.85x3.9x1.52	8	gull wing	
Comment	07 SO 08 .15 JEDEC; MDF is valid for TS3702IDT			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-March 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	TRUE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	FALSE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description

QueryList : ELV directive : 2000/53/EC amended 2017/2096 _November 2017	
Query	Response
1 - Product(s) meets EU ELV requirements without any exemptions	TRUE
2 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	FALSE
Exemption Id.	Description

QueryList : REACH-27th June 2018				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				TRUE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product
;				0
2 - Product(s) does not contain REACH Substances Of Very High Concern in any Embedded article nor Homogeneous Material above the limits per the definition within REACH				TRUE
CategoryLevel_Name	CategoryLevel_Threshold	Amount in Embedded Article / Homogeneous Material (mg)	Application - Article / Homogeneous Material	ppm in Article /Homogeneous Material

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	CDO7*3702AAW				6000001.0	1000004.0
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	M-011 Other inorganic materials	1.038	mg	supplier	die	Silicon (Si)	7440-21-3		1.012	mg	974952	12650
				supplier	metallization	Aluminium (Al)	7429-90-5		0.004	mg	3854	50
				supplier	Passivation	Silicon Nitride	12033-89-5		0.003	mg	2890	38
				supplier	Passivation	Silicon Oxide	7631-86-9		0.019	mg	18304	238
Leadframe	M-004 Copper and its alloys	33.619	mg	supplier	alloy	Copper (Cu)	7440-50-8		32.499	mg	966686	406238
				supplier	alloy	Iron (Fe)	7439-89-6		0.764	mg	22725	9550
				supplier	alloy	Iron Phosphide (FeP)	36508-33-8		0.046	mg	1368	575
				supplier	alloy	Zinc (Zn)	7440-66-6		0.040	mg	1190	500
				supplier	metallization	Silver (Ag)	7440-22-4		0.270	mg	8031	3375
Die attach	M-015 Other organic materials	0.404	mg	supplier	glue	Silver (Ag)	7440-22-4		0.356	mg	881188	4450
				supplier	glue	Isobornyl Methacrylate	7534-94-3		0.020	mg	49505	250
				supplier	glue	Acrylate resin	5888-33-5		0.020	mg	49505	250
				supplier	glue	Methyl acrylate polymer	87320-05-6		0.008	mg	19802	100
Bonding wires	M-011 Other inorganic materials	0.040	mg	supplier	wire	Copper (Cu)	7440-50-8		0.040	mg	1000000	500
Encapsulation	M-015 Other organic materials	43.828	mg	supplier	mold compound	Silica, vitreous	60676-86-0		37.956	mg	866022	474450
				supplier	mold compound	Epoxy Resin	85954-11-6		3.287	mg	74998	41088
				supplier	mold compound	Phenol Resin	26834-02-6		2.191	mg	49991	27388
				supplier	mold compound	Carbon black	1333-86-4		0.219	mg	4997	2738
				supplier	mold compound	Bismuth compound	7440-69-9		0.175	mg	3993	2188
connections coating	Solder	1.071	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		1.071	mg	1000000	13388