

Reference	Part Value	Description	Package	Manufacturer	Part Number
C1,C19,C20,C21,C24,C41,C43,C47,C53,C55,C56,C62,C63,C64,C65,C67,C77,C78	100nF/25V	SMT Ceramic Capacitor	Size 0603	WURTH ELEKTRONIK	885012206071
C2	220nF/25V	SMT Ceramic Capacitor	Size 0603	WURTH ELEKTRONIK	885012106019
C3,C12,C26	1uF/50V	SMT Ceramic Capacitor	Size 0805	WURTH ELEKTRONIK	885012207103
C4,C7,C13,C17,C25,C33,C40,C69,C70,C74	N.M.	SMT Ceramic Capacitor	Size 0603		
C8	N.M.	Film, Metallized Polypropylene	5x13 mm, Pitch 10 mm	WURTH ELEKTRONIK	890283423001
or C9	33nF/630V	SMT Ceramic Capacitor	Size 1210	WURTH ELEKTRONIK	885342209004
C10,C11,C59,C60	10pF/50V	SMT Ceramic Capacitor	Size 0603	WURTH ELEKTRONIK	885012006051
C16	4.7nF/25V	SMT Ceramic Capacitor	Size 0603	WURTH ELEKTRONIK	885012206063
C18,C73	47nF/25V	SMT Ceramic Capacitor	Size 0603	WURTH ELEKTRONIK	885012206069
C27,C30,C71	33pF/25V	SMT Ceramic Capacitor	Size 0603	WURTH ELEKTRONIK	885012006035
C32,C68,C72	4.7pF/25V	SMT Ceramic Capacitor	Size 0603	WURTH ELEKTRONIK	885012006030
C34	3.3nF/25V	SMT Ceramic Capacitor	Size 0603	WURTH ELEKTRONIK	885012206062
C36,C42,C75	1nF/25V	SMT Ceramic Capacitor	Size 0603	WURTH ELEKTRONIK	885012206059
C37,C38,C39	10pF/10V	SMT Ceramic Capacitor	Size 0603	WURTH ELEKTRONIK	885012006002
C44	150uF/420V	THT Electrolytic Capacitor, Radial p10 d22h27 105C	Radial p10 d22h27.5 mm	United Chemi-Con	EKMZ421VSN151MP25S
C44A	N.M.	THT Electrolytic Capacitor, Radial p7.5 d18h25	Radial p7.5 d18h25 mm	Rubycon	450BXW68MEFC18X25
C45	22uF/25V	SMT Aluminum Elect. Capacitor	5x5.4 mm	WURTH ELEKTRONIK	865090442004
C46	470uF/10V	SMT Aluminum Elect. Capacitor	6.3x7.7 mm	Panasonic	EEEFTA471XAP
C48	10uF/10V	SMT Ceramic Capacitor	Size 1206	WURTH ELEKTRONIK	885012208018
C49	47uF/25V	SMT Aluminum Elect. Capacitor	6.3x5.8 mm	WURTH ELEKTRONIK	865060443004
C50	10uF/35V	SMT Aluminum Elect. Capacitor	5x5.4 mm	WURTH ELEKTRONIK	865230542002
C51	820pF/25V	SMT Ceramic Capacitor	Size 0603		
C52	680nF/10V	SMT Ceramic Capacitor	Size 0603	WURTH ELEKTRONIK	885012206025
C54,C58	1uF/10V	SMT Ceramic Capacitor	Size 0603	WURTH ELEKTRONIK	885012206026
C57	10nF/25V	SMT Ceramic Capacitor	Size 0603	WURTH ELEKTRONIK	885012206065
C61	100nF/50V	SMT Ceramic Capacitor	Size 0603	WURTH ELEKTRONIK	885012206095
C66	220pF/ 630V	SMT Ceramic Capacitor	Size 1206	Multicomp	MC1206N221J631CT
C76	4.7uF/50V	SMT Ceramic Capacitor	Size 1206	WURTH ELEKTRONIK	885012208094
DL1,DL2	YELLOW	Yellow LED	Size 0603	WURTH ELEKTRONIK	150060YS75000
DL3	RED	Red LED	Size 0603	WURTH ELEKTRONIK	150060RS75000
D1,D6,D11	N.M.	Turbo 2 Ultrafast High-Voltage Rectifier	SMA	STMicroelectronics	STTH1L06A
D2,D4,D7,D9,D12,D13,D19,D27	BAT54J	40V, 300mA Small signal Schottky SMT Diode	SOD-323	STMicroelectronics	BAT54JFILM
D20	GBU805	8A Glass Passivated Single-Phase Bridge Rectifier	GBU	Taiwan Semiconductor or Diodes Incorporated	GBU805 or GBU806
D21	DDZ9690T	SURFACE MOUNT ZENER DIODE	SOD523	DIODES Incorporated	DDZ9690T-7
D22	3V3 N.M.	ZENER	SOD-123		
D25	STPS0560Z	60V, 0.5A Schottky rectifier	SOD-123	STMicroelectronics	STPS0560Z
D26	STPS1150A	150V, 1A Power Schottky rectifier	SMA	STMicroelectronics	STPS1150A
D28	STTH1L06A	Turbo 2 Ultrafast High Voltage Rectifier	SMA	STMicroelectronics	STTH1L06A
F1A	N.M.	Time Lag radial lead Micro Fuse, 250Vac	RST-BELFUSE	belfuse	0697-xx
F1	10A/277V slow	Suface Mount Fuse, Time-Lag T, 250Vac125Vdc	UMT250-SHURTER	Schurter	3403.0176.24
JP1	CLOSED 2-3	SMT Jumper	Soldering pad		
JP2,JP3,JP4,JP5,JP6	CLOSED	SMT Jumper	Soldering pad		
JP7	CLOSED 2-4	Jumper to solder	Soldering pads		
JP8,JP9	CLOSED 1-2	Strip connector 3 pos, 2.54 mm	1x3 pins	WURTH ELEKTRONIK	61300311121
JP10	OPEN	SMT Jumper	Size 0805		
JP11	OPEN	SMT jumper			
JP13,JP14,JP15	N.M.				
J1,J7,J9	STRIP 1x4	Strip connector 4 pos, 2.54 mm	1x4 pins	WURTH ELEKTRONIK	61300411121
J2	MORSV-508-3P_screw	Connector terminal block T.H. 3 positions 5.08 mm	3 poles, Pitch 5.08	WURTH ELEKTRONIK	691213510003

J3	STRIP 1x5	Strip connector 5 pos, 2.54 mm	1x5 pins	WURTH ELEKTRONIK	61300511121
J4	MORSV-508-2P_screw	Connector terminal block T.H. 2 positions 5.08 mm	2 poles, Pitch 5.08	WURTH ELEKTRONIK	691213510002
J5	65100516121	MINI USB 2.0 TYPE B SMD	USB MINI B	WURTH ELEKTRONIK	65100516121
TP6,J6,J8	STRIP 1x2	Strip connector 2 pos, 2.54 mm	1x2 pins	WURTH ELEKTRONIK	61300211121
LD1	RED-GREEN	LED indicators,PLCC-4 Red / Yellow Green	PLCC 4	AVAGO	HSMF-A201-A00J1
LD2	GREEN	Green LED	Size 0805	WURTH ELEKTRONIK	150080GS75000
NTC1	2R2	NTC Thermistor for Inrush current limiting		TDK	B5723650229M000
Q1A,Q3A,Q4A,Q6A,Q7A,Q9A	N.M.	N-channel 600 V, 0.195 Ohm typ., 15 A MDMesh DM2 Power MOSFET	PowerFLAT 8x8	STMicroelectronics	STL24N60DM2
Q1,Q3,Q4,Q6,Q7,Q9	STGD6M65DF2	Trench gate field-stop IGBT, M series 650V, 6A low loss	DKPAK	STMicroelectronics	STGD6M65DF2
Q10	BC847	GENERAL PURPOSE 45V 100mA 225mW	SOT23	ON SEMICONDUCTOR	BC847BL
Q12	3STF1640	Low voltage high performance NPN power transistor	SOT-89	STMicroelectronics	3STF1640
RV1	N.M.	Varistor	Pitch 2.3x7.5 mm		
R1,R15,R35	27R	SMT resistor	Size 0805		
R2,R10,R16,R27,R40,R44	10R	SMT Resistor	Size 0805		
R3,R13,R18,R30,R42,R45	100R	SMT Resistor	Size 0805		
R5,R14,R19,R31,R43,R46,R105,R106	100K	SMT Resistor	Size 0603		
R23	100K	Square trimpot trimming potentiometer	3386H	BOURNS	3386H-1-104-LF
R26,R29,R73,R95,R97,R99,R101,R118,R119,R125	0R	SMT resistor	Size 0603		
R32	47K	SMT Resistor	Size 0603		
R33,R53,R56	220m/ 1W/ 1%	SMT Resistor	Size 2512 / 1210		
R41,R111,R114,R115,R120,R124	20K	SMT Resistor	Size 0603		
R47	0R	SMT Resistor	Size 0603		
R48	39K	SMT Resistor	Size 0603		
R49,R52,R63,R64,R89,R90,R103,R116,R122,R126	10K	SMT Resistor	Size 0603		
R50,R51,R57	1K	SMT Resistor	Size 0603		
R54,R66,R79,R91,R102,R107,R108	100R	SMT Resistor	Size 0603		
R55,R112,R113,R117,R121,R123	6K8	SMT Resistor	Size 0603		
R62,R77	120R	SMT Resistor	Size 0603		
R67,R69	470K	SMT Resistor	Size 1206		
R68,R70,R71	1.8K	SMT Resistor	Size 0603		
R72	N.M.	NTC Resistor	Hole 0.8 mm		
R74,R75,R76,R104	N.M.	SMT Resistor	Size 0603		
R78	6.49K	SMT Resistor	Size 0805		
R80	1K	SMT Resistor	Size 0805		
R81,R94,R98,R100	4.7K	SMT Resistor	Size 0603		
R82	330R	SMT Resistor	Size 0603		
R83	0R	SMT Resistor	Size 1206		
R84,R93	36K	SMT Resistor	Size 0603		
R85	10R	SMT Resistor	Size 0603		
R86,R87	22K	SMT Resistor	Size 0603		
R88	1.5K	SMT Resistor	Size 1206		
R92	1.5K	SMT Resistor	Size 0603		
R96	2.7K	SMT Resistor	Size 0603		
R110	220K 1/3W	SMT Resistor	Size 0805	TE Connectivity	CRGH0805J220K
R127	8K2	SMT Resistor	Size 0603		
R128,R129	33K	SMT Resistor	Size 0603		
SW1,SW2,SW3	430483025816	CMS TACTILE SWITCHES - 6x6 J-bend		WURTH ELEKTRONIK	430483025816
TP1	TPHIN1	Test point, PCB 1mm DIAMETER	Copper Pad		
TP2	TPHIN2	Test point, PCB 1mm DIAMETER	Copper Pad		
TP3	TPHIN3	Test point, PCB 1mm DIAMETER	Copper Pad		
TP4,TP7,TP14,TP19,TP20,TP21,TP22,TP23,TP24,TP25,TP26,TP27,TP29	N.M.	TP for Probe	Diam. 1.27, Hole 0.8mm		
TP5	PB8	Test point, PCB 1mm DIAMETER	Copper Pad		
TP8,TP12	TPH-ANELLO-1mm	THT Ring Test Point		Keystone	5003

TP15	NEEDLE-PAD-1.7mm	Test Point - PCB 1.7mm DIAMETER	Copper Pad		
TP18	PGND	Test point, PCB 1mm DIAMETER	Copper Pad		
TP28	PA12	Test point, PCB 1mm DIAMETER	Copper Pad		
T1	750318434	Switch mode Transformer 2.3W 60kHz 3.15mH 7-15V		WURTH ELECTRONIK	750318434
U1	STSPIN32F0601	600V three-phase controller with ARM Cortex MCU	TQFP64- 10x10x1.0	STMicroelectronics	STSPIN32F0601/TR
U4	LD1117S33CTR	800mA, 3.3V Adjustable and Fixed low drop positive voltage regulator	SOT-223	STMicroelectronics	LD1117S33CTR
U5	VIPER06XS	Fixed-frequency VIPer plus family	SSO10	STMicroelectronics	VIPER06XS
U6	USBLC6-2SC6	Very low capacitance ESD protection	SOT23-6L	STMicroelectronics	USBLC6-2SC6 / Y
U7	LD3985M33R	3.3V_150mA_ULTRA LOW DROP VOLTAGE REGULATOR	SOT23-5L	STMicroelectronics	LD3985M33R
U8	STM32F103CBT6	64/182KB FLASH_USB_72MHz_3.6V	LQFP48 - 7x7 mm	STMicroelectronics	STM32F103CBT6
U10,U11	TSV912IQ2T	Dual rail-to rail input/output 8 MHz operational amplifiers	DFN8 2x2	STMicroelectronics	TSV912IQ2T
X1,X2	8MHz	CRYSTAL 8.0000MHZ 8PF SMD	2.5x3.2 mm	NDK	NX3225GD-8MHZ-STD-CRA-3
		Rubber feet		Hammond	1421T6CL
J8,JP8,JP9		Female Jumper Isolated, pitch 2.54mm		ASSMANN WSW	AKSCT/Z BLACK
		P.C.B. EVSPIN32F0601S3 Rev.2.0		STMicroelectronics	