



PWDN: active high, with internal pull-down resistor
 RESET: active low, with internal pull-up resistor

Power:
 1. AVDD: 2.8V
 2. AF-VCC (for Motor): 2.8V
 3. DVDD: 1.5V, external 1.5V or internal 1.5V from internal regulator via DOVDD
 4. DOVDD: 1.8V or 2.8V config by Solder bridge



