

Bill of Materials

| Item | Q.ty | Reference | Part/Value | Type/Additional notes | Tolerance |
|------|------|----------------------------------|---|---------------------------|-----------|
| 1 | 1 | CN5 | Arduino connector CN5 10 pins | | |
| 2 | 2 | CN6, CN9 | Arduino connectors CN6 and CN9 8 pins | | |
| 3 | 2 | CN7, CN10 | MORPHO connectors CN7 and CN10 38 pins | Not mounted | |
| 4 | 1 | CN8 | Arduino connector CN8 6 pins | | |
| 5 | 1 | C1 | 100 nF 16 V | Ceramic X7R | ± 10% |
| 6 | 1 | C2 | 1 µF 16 V | Ceramic X5R | ± 10% |
| 7 | 1 | J1 | Jumper | | |
| 8 | 7 | R1, R2, R3, R4, R6, R7, R8 | 0 | R6, R7, R8 not mounted | ± 1% |
| 9 | 2 | R5, R12 | 100 k | | ± 1% |
| 10 | 1 | R9 | 47 k | | ± 1% |
| 11 | 2 | R10, R11 | 10 k | | ± 1% |
| 12 | 1 | U1 | SPBTLE-RF | | |
| 13 | 1 | U2 | M95640-RMC6TG | | |

Bill of Materials (additional columns)

| Item | Package | Manufacturer | Manuf. order code part number |
|-------------|---|---------------------|--------------------------------------|
| 1 | Pass-through: male on bottom, female on top. 10x1 2.54 mm pitch | SAMTEC | SSQ-110-03-F-S |
| 2 | Pass-through: male on bottom, female on top. 8x1 2.54 mm pitch | SAMTEC | SSQ-108-03-F-S |
| 3 | Pass-through: female on bottom, male on top. 19x2 2.54 mm pitch | | |
| 4 | Pass-through: male on bottom, female on top. 6x1 2.54 mm pitch | SAMTEC | SSQ-106-03-G-S |
| 5 | SMD 0402 | Murata | GRM155R71C104KA88 |
| 6 | SMD 0402 | TDK | C1005X5R1C105K050BC |
| 7 | Through hole 26x1 2.54 mm pitch | ANY | ANY |
| 8 | SMD 0805 | ANY | ANY |
| 9 | SMD 0805 | ANY | ANY |
| 10 | SMD 0805 | ANY | ANY |
| 11 | SMD 0805 | ANY | ANY |
| 12 | SMD 11 pins | ST | SPBTLE-RF |
| 13 | UFDFPN8 (MLP8) | ST | M95640-RMC6TG |