

Table 1: STEVAL-ESC001V1 bill of materials

Item	Q.ty	Ref.	Part / Value	Description	Manufacturer	Order code
1	15	C1, C2, C5, C8, C10 C12, C13, C14, C18 C19, C23, C44, C55 C56, C57	100 nF 25 V ±10% X7R	Ceramic capacitor	any	-
2	3	C3, C4, C11	1 nF 50 V ±10% X7R	Ceramic capacitor	any	-
3	1	C6	4.7 µF 10 V ±10% X5R	Ceramic capacitor	Murata	GRM188R61A475KE15D
4	2	C7, C59	10 nF 50 V ±10% X7R	Ceramic capacitor	any	-
5	3	C9, C43, C46	1 µF 16 V ±10% X7R	Ceramic capacitor	TDK	C1608X7R1C105K080AC
6	3	C15, C16, C17	15 nF 10 V ±10% X7R	Ceramic capacitor	any	-
7	3	C20, C21, C22	680 pF 10 V ±5% C0G	Ceramic capacitor	any	-
8	3	C24, C25, C26	100 pF ±0%	Capacitors (not mounted)	-	-
9	1	C27	3.9 nF 50 V ±10% X7R	Ceramic capacitor	any	-
10	1	C28	220 nF 50 V ±10% X7R	Ceramic capacitor	any	-
11	1	C29	10 µF 50 V ±10% X5R	Ceramic capacitor	any	-
12	1	C30	22 µF 25 V ±10% X5R	Ceramic capacitor	any	-
13	3	C31, C42, C50	1 µF X7R 50 V ±10%	Ceramic capacitor	any	-
14	2	C32, C35	330 µF, 35 V ±20%	Electrolytic capacitor	Rubycon	35ZLH330MEFC10X12.5
15	2	C33, C34	100 nF 100 V ±10% X7R	Ceramic capacitor	any	-
16	1	C36	27 pF 50 V ±5% C0G	Ceramic capacitor	any	-
17	2	C37, C60	4.7 nF 16 V ±10% X7R	Ceramic capacitor	any	-
18	6	C38, C39, C47 C48, C52, C53	100 pF 16 V ±10% X7R	Ceramic capacitor	any	-
19	3	C40, C49, C54	470 nF 25 V ±10% X7R	Ceramic capacitor	any	-
20	3	C41, C51, C58	10 nF 100 V ±10% X7R	Ceramic capacitor	any	-
21	1	C45	10 µF 25 V ±10% X7R	Ceramic capacitor	Murata	GRM21BR61E106KA73L
22	1	D1	-	Red LED	Lite-on	LTST-C193KRKT-5A
23	1	D2	-	Red LED	Lite-on	LTST-C193KGKT-5A

Item	Q.ty	Ref.	Part / Value	Description	Manufacturer	Order code
24	1	D3	40 V 1 A	Low drop power Schottky diode	ST	STPS1L40M
25	3	D4, D8, D11	60V/0.5A	Power Schottky diode	ST	STPS0560Z
26	1	D5	-	Transil	ST	SMBJ26A-TR
27	7	D6, D7, D9, D10 D12, D13, D14	30V, 0.3A	Schottky diode	ST	BAT30KFILM
28	2	J1, J2	-	CAN, UART: 4 WAYS STRIP LINE - MALE 1.27mm	any	-
29	1	J3	-	PWM INPUT: 3 way wires welding	-	-
30	1	J4	-	SWD: 4-way strip line - male 2.54mm	any	-
31	2	J5, J6	-	CON1 - Input power connector: 1-way wire welding	-	-
32	1	J7	-	Motor Connetor: 3-way wire welding	-	-
33	1	L1	33 μ H 0.5 A	Power inductor	Coilcraft	LPS4018-333MRB
34	6	Q1, Q2, Q3 Q4, Q5, Q6	30 V, 160 A	Power MOSFETs	ST	STL160NS3LLH7
			40 V, 160 A			STL160N4F7
35	6	R1, R5, R28 R39, R41, R48	0 62.5 mW \pm 5%	SMD resistor	any	-
36	1	R2	120 62.5 mW \pm 5%	SMD resistor	any	-
37	1	R3	10 k 62.5 mW \pm 5%	SMD resistor	any	-
38	1	R4	220 62.5 mW \pm 5%	SMD resistor	any	-
39	1	R6	62.5 mW \pm 5%	SMD resistor	any	-
40	2	R7, R8	510 62.5 mW \pm 5%	SMD resistor	any	-
41	1	R9	33 K 62.5 mW \pm 5%	SMD resistor	any	-
42	3	R10, R11, R12	680 62.5 mW \pm 5%	SMD resistor	any	-
43	1	R13	5.9 K 62.5 mW \pm 5%	SMD resistor	any	-
44	3	R14, R15, R16	8.06 k 62.5 mW \pm 1%	SMD resistor	Vishay	CRCW04028K06FKED
45	3	R17, R19, R20	787 62.5 mW \pm 1%	SMD resistor	Panasonic	ERJ2RKF7870X
46	3	R18, R21, R22	3.4 k 62.5 mW \pm 1%	SMD resistor	Panasonic	ERJ2RKF3401X
47	2	R23, R24, R25	13 k 62.5 mW \pm 1%	SMD resistor	any	-
48	1	R26	4.7 k 62.5 mW \pm 1%	SMD resistor	any	-

Item	Q.ty	Ref.	Part / Value	Description	Manufacturer	Order code
49	1	R65	4.7 k 62.5 mW ±5%	SMD resistor	any	-
50	1	R27	62 62.5 mW ±1%	SMD resistor	any	-
51	1	R29	34.8 k 62.5 mW ±1%	SMD resistor	any	-
52	6	R30, R35, R40 R44, R49, R55	56 0.1 W ±5%	SMD resistor	any	-
53	1	R31	300 62.5 mW ±1%	SMD resistor	any	-
54	1	R32	8.2 k 62.5 mW ±1%	SMD resistor	any	-
55	6	R33, R37, R42 R45, R50, R59	100 0.1 W ±5%	SMD resistor	any	-
56	6	R34, R38, R43 R47, R51, R61	10 k 0.1 W ±5%	SMD resistor	any	-
57	3	R36, R46, R58	1 0.125 W ±5%	SMD resistor	any	-
58	3	R52, R53, R54	33 k 0.1 W ±1%	SMD resistor	any	-
59	3	R56, R57, R60	4.02 k 62.5 mW ±1%	SMD resistor	any	-
60	1	R62	169 K 62.5 mW ±1%	SMD resistor	any	-
61	1	R63	NTC 10 K ±1%	NTC Thermistor	TDK	NTCG103JF103F
62	3	R64, R66, R67	0.01 3 W ±1%	10 mOhm shunt resistor	Bourns	CRA2512-FZ-R010ELF
					KOA Speer	TLR3APDTE10L0F50
63	1	R68	18 K 62.5 mW ±1%	SMD resistor	any	-
64	1	TP1, TP2, TP3, TP4 TP5, TP6, TP7, TP8 TP9, TP10, TP11 TP12, TP13, TP14 TP15	SMD PAD 1 mm ±0%	Test point	any	-
65	1	U1	-	CAN transceiver	TI	SN65HVD230D
66	1	U2	-	32bit MCU	ST	STM32F303CBT7
67	3	U3, U4, U5	-	Rail-to-rail input/ output 20 MHz GBP operational amplifiers	ST	TSV991ILT
68	1	U6	-	3 A step-down switching regulator	ST	L7986TR
69	3	U7, U10, U11	-	High voltage high and low-side driver	ST	L6398D
70	1	U8	-	Low drop vo ltage regulator	ST	LD39050PU33R

Item	Q.ty	Ref.	Part / Value	Description	Manufacturer	Order code
71	1	U9	-	Low drop voltage regulator	ST	LD1117S50TR
72	1	X1	-	Resonators 8 Mhz	Murata	CSTCE8M00G55-R0

**STMicroelectronics****EVALUATION BOARD LICENSE AGREEMENT**

By using this evaluation board or kit (together with all related software, firmware, components, and documentation provided by ST, "Evaluation Board"), You ("You") are agreeing to be bound by the terms and conditions of this Evaluation Board License Agreement ("Agreement"). Do not use the Evaluation Board until You have read and agreed to this Agreement. Your use of the Evaluation Board constitutes Your acceptance of this Agreement.

LICENSE

STMicroelectronics ("ST") grants You the right to use the enclosed Evaluation Board offering limited features only to evaluate and test ST products solely for Your evaluation and testing purposes in a research and development setting. The Evaluation Board shall not be, in any case, directly or indirectly assembled as a part in any production of Yours as it is solely developed to serve evaluation purposes and has no direct function and is not a finished product. If software and/or firmware is accompanied by a separate end user license agreement ("EULA"), then such software and/or firmware shall be governed by such EULA.

EVALUATION BOARD STATUS

The Evaluation Board offers limited features allowing You only to evaluate and test the ST products. The Evaluation Board is not intended for consumer or household use. You are not authorized to use the Evaluation Board in any production system, and it may not be offered for sale or lease, or sold, leased or otherwise distributed for commercial purposes. If the Evaluation Board is incorporated in an evaluation system, the evaluation system may be used by You solely for Your evaluation and testing purposes. Such evaluation system may not be offered for sale or lease or sold, leased or otherwise distributed for commercial purposes and must be accompanied by a conspicuous notice as follows: "This device is not, and may not be, offered for sale or lease, or sold or leased or otherwise distributed for commercial purposes".

OWNERSHIP AND COPYRIGHT

Title to the Evaluation Board remains with ST and/or its licensors. You may not remove any copyright or other proprietary rights notices without prior written authorization from ST. You may make one copy of the software and/or firmware of the Evaluation Board for back up or archival purposes provided that You reproduce and apply to such copy any copyright or other proprietary rights notices included on or embedded in the software and/or firmware. You agree to prevent any unauthorized copying in whole or in part of the Evaluation Board.

RESTRICTIONS AND WARNINGS

Before You handle or use the Evaluation Board, You must carefully review any related documentation provided by ST. Such documentation may contain important warnings. You shall comply with all such warnings and other instructions and employ reasonable safety precautions in using the Evaluation Board. Failure to do so may result in death, personal injury, or property damage. If You have any questions regarding the safe usage of the Evaluation Board, You should contact ST for guidance. You may not sell, assign, sublicense, lease, rent or otherwise distribute the Evaluation Board for commercial purposes, in whole or in part, or use Evaluation Board in a production system, with the exception that if You are an authorized ST distributor, You may resell the Evaluation Board in compliance with the applicable terms and conditions. Except as provided in this Agreement or as explicitly permitted in the documentation of the Evaluation Board, You may not reproduce the Evaluation Board or modify, reverse engineer, de-compile or disassemble its software and/or firmware, in whole or in part. You shall not use the Evaluation Board in any safety critical or functional safety testing, including but not limited to testing of life supporting, military or nuclear applications. ST expressly disclaims any responsibility for such usage which shall be made at Your sole risk, even if ST has been informed in writing of such usage. Unless expressly designated in writing by ST as suitable for use in testing automotive or aerospace applications, You shall not use the Evaluation Board in such testing.

Notice applicable to Evaluation Boards according to European Regulation

For the European Regulation of the Evaluation Board, the applicable EU directives are considered, with a particular attention to the Low Voltage Directive (LVD) 2014/35/EU, the Electromagnetic Compatibility (EMC) Directive 2014/30/EU, and the Radio Equipment Directive (RED) 2014/53/EU. If the Evaluation Board is outside the scope of the foregoing Directives, then the General Product Safety Directive (GPSD) 2001/95/EC and Council Directive 93/68/EEC, amending Directive 73/23/EEC on electrical equipment designed for use within certain voltage limits, are applicable.

The Evaluation Board meets the requirements of the Restriction of Hazardous Substances (RoHS 2 or RoHS recast) Directive 2011/65/EU, Annex II, as amended by Directive 2015/863/EU.

Notice applicable to Evaluation Boards not FCC-Approved

This kit is designed to allow:

- (1) Product developers to evaluate electronic components, circuitry, or software associated with the kit to determine whether to incorporate such items in a finished product and
- (2) Software developers to write software applications for use with the end product.

This kit is not a finished product and when assembled may not be resold or otherwise marketed unless all required FCC equipment authorizations are first obtained. Operation is subject to the condition that this product not cause harmful interference to licensed radio stations and that this product accept harmful interference. Unless the assembled kit is designed to operate under part 15, part 18 or part 95 of 47 CFR, Chapter I ("FCC Rules"), the operator of the kit must operate under the authority of an FCC license holder or must secure an experimental authorization under part 5 of this chapter.

For Evaluation Boards annotated as FEDERAL COMMUNICATIONS COMMISSION (FCC) Part 15 Compliant

- **FCC Interference Statement for Class A Evaluation Boards:** This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his own expense.
- **FCC Interference Statement for Class B Evaluation Boards:** This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:
 - Reorient or relocate the receiving antenna.
 - Increase the separation between the equipment and receiver.
 - Connect the equipment to an outlet on a circuit different from that to which the receiver is connected.
 - Consult the dealer or an experienced radio/TV technician for help.
- This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

WARRANTY

ST WARRANTS THAT IT HAS THE RIGHT TO PROVIDE THE EVALUATION BOARD TO YOU. THIS WARRANTY IS PROVIDED BY ST IN LIEU OF ALL OTHER WARRANTIES, WRITTEN OR ORAL, STATUTORY, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY AS TO MERCHANTABILITY, NON-INFRINGEMENT, FITNESS FOR ANY PARTICULAR PURPOSE, OR UNINTERRUPTED OR ERROR-FREE OPERATION, ALL OF WHICH ARE EXPRESSLY DISCLAIMED. THE EVALUATION BOARD IS PROVIDED "AS IS".

YOU WARRANT TO ST THAT YOU WILL ENSURE THE EVALUATION BOARD IS USED ONLY BY ELECTRONICS EXPERTS WHO UNDERSTAND THE DANGERS OF HANDLING AND USING SUCH ITEMS, YOU ASSUME ALL RESPONSIBILITY AND LIABILITY FOR ANY IMPROPER OR UNSAFE HANDLING OR USE OF THE EVALUATION BOARD BY YOU, YOUR EMPLOYEES, AFFILIATES, CONTRACTORS, AND DESIGNEES.

LIMITATION OF LIABILITIES

IN NO EVENT SHALL ST BE LIABLE TO YOU, WHETHER IN CONTRACT, TORT (INCLUDING NEGLIGENCE), STRICT LIABILITY, OR ANY OTHER LEGAL THEORY, FOR ANY INDIRECT, SPECIAL, CONSEQUENTIAL, INCIDENTAL, PUNITIVE, OR EXEMPLARY DAMAGES WITH RESPECT TO ANY MATTERS RELATING TO THIS AGREEMENT, REGARDLESS OF WHETHER ST HAS BEEN ADVISED OF THE POSSIBILITY OF THE SAME. IN NO EVENT SHALL ST'S LIABILITY ARISING OUT OF THIS AGREEMENT IN THE AGGREGATE EXCEED THE AMOUNT PAID BY YOU UNDER THIS AGREEMENT FOR THE PURCHASE OF THE EVALUATION BOARD, OR TEN UNITED STATES DOLLARS (\$10.00) IF NO PURCHASE PRICE WAS PAID.

INDEMNIFICATION

You shall, at Your expense, defend ST and its Affiliates against a claim or action brought by a third party for infringement or misappropriation of any patent, copyright, trade secret or other intellectual property right of a third party to the extent resulting from (1) Your combination of the Evaluation Board with any other component, system, software, or firmware, (2) Your modification of the Evaluation Board, or (3) Your use of the Evaluation Board in a manner not permitted under this Agreement. You shall indemnify ST and its Affiliates against and pay any resulting costs and damages finally awarded against ST or its Affiliates or agreed to in any settlement, provided that You have sole control of the defense and settlement of the claim or action, and ST cooperates in the defense and furnishes all related evidence under its control at Your expense. ST will be entitled to participate in the defense of such claim or action and to employ counsel at its own expense.

"Affiliates" means any corporation or other entity directly or indirectly controlled by, controlling or under common control with the entity in question, for so long as such ownership exists. "Control" means the direct or indirect beneficial ownership of more than fifty (50%) percent of the stock or other equity interests entitled to vote for the election of directors or an equivalent governing body. Any such corporation or other legal entity shall be deemed to be an Affiliate of such Party only as long as such Control exists.

TERMINATION

ST may terminate this Agreement without notice if You breach this Agreement. Upon termination, You shall immediately destroy or return all copies of the software, firmware, and documentation of the Evaluation Board to ST and certify in writing to ST that You have done so.

APPLICABLE LAW AND JURISDICTION

This Agreement shall be governed, construed and enforced in accordance with the laws of Switzerland, without regard to its conflict of laws rules. The UN Convention on Contracts for the International Sale of Goods shall not apply to this Agreement. In case of dispute and in the absence of an amicable settlement, the only competent jurisdiction shall be the Courts of Geneva, Switzerland. Any breach of this Agreement by You may result in irreparable damage to ST for which ST will not have an

adequate remedy at law. Accordingly, in addition to any other remedies and damages available, You acknowledge and agree that ST may immediately seek enforcement of this Agreement in any jurisdiction by means of specific performance or injunction, without any requirement to post a bond or other security.

SEVERABILITY

If any provision of this agreement is or becomes, at any time or for any reason, unenforceable or invalid, no other provision of this agreement shall be affected thereby, and the remaining provisions of this agreement shall continue with the same force and effect as if such unenforceable or invalid provisions had not been inserted in this Agreement. In addition, any unenforceable or invalid provision shall be deemed replaced by a provision that is valid and enforceable and that comes closest to expressing the intention of the unenforceable or invalid provision.

WAIVER

The waiver by either party of any breach of any provision of this Agreement shall not operate or be construed as a waiver of any other or a subsequent breach of the same or a different provision.

RELATIONSHIP OF THE PARTIES

Nothing in this Agreement shall create, or be deemed to create, any joint venture, partnership, principal-agent, employer-employee or other relationship between the Parties, except that of independent contractors. Neither Party has the authority or power to bind, to contract in the name of, or to create a liability for the other in any way or for any purpose.

SURVIVAL

Any provision of this Agreement which imposes an obligation after termination of this Agreement shall survive the termination of this Agreement.

SECTION HEADINGS

Section headings are inserted for convenience only and shall not be used to interpret this Agreement.

WASTE AND RECYCLING

The Evaluation Board is not to be disposed of as urban waste. At the end of its life cycle, differentiated waste collection must be followed. Consult the local authorities for more information on the proper disposal channels. It is mandatory to separately collect the Evaluation Board and make sure it is delivered to the appropriate waste management and recycling centers.

As of 15 August 2018, in all the countries belonging to the European Union, the Evaluation Board is subject to the WEEE Directive 2012/19/EU requirement; therefore, it is forbidden to dispose of the Evaluation Board as undifferentiated waste or with other domestic wastes. Consult the local authorities for more information on the proper recycling centers.

Disposing of the Evaluation Board incorrectly may cause damage to the environment and may be subject to fines based on specific countries' rules.