



# Material Composition Declaration

© Copyright 2005. IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.

This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.

**Adobe Reader version 7.0.5 is required to complete this declaration.**

1752-2 1.1	IPC Web Site for Information on IPC-1752 Standard <a href="http://www.ipc.org/IPC-175x">http://www.ipc.org/IPC-175x</a>	<b>Form Type *</b> Distribute	<b>Declaration Class *</b> Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Informat
------------	--	----------------------------------	---

## Supplier Information

<b>Company Name *</b> STMicroelectronics	Company Unique ID	Unique ID Authority	<b>Response Date *</b> NA	Response Document ID				
<b>Contact Name *</b>	Title - Contact	<b>Phone - Contact *</b>	<b>Email - Contact *</b>	Duplicate Contact -> Authorized Representative				
<b>Authorized Representative *</b> Giacoppo Giovanni	Title - Representative APM MD CHAMPION	<b>Phone - Representative *</b> NA	<b>Email - Representative *</b> NA	Supplier Comments or URL for Additional Information				
Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	<b>Weight *</b>	UOM	Unit Type
	T1635T-8l	7BVT*A16C8HC	2010-09-03	A	SH1A	2,140	mg	Each
Alternate Recommendation	TO 220 I CLIP Package			Alternate Item Comments		ECOPACK1/ROHS BSA REF: CD00281661		

## Manufacturing Process Information

Terminal Plating / Grid Array Material <b>Matte Tin (Sn)</b>	Terminal Base Alloy <b>CU Alloy</b>	J-STD-020 MSL Rating <b>Not Applicable</b>	Peak Process Body Temperature <b>C</b>	Max Time at Peak Temperature seconds	Number of Reflow Cycles
---	--	---	---	---	-------------------------

Comments

**Disclaimer: While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and**

Save the fields in this form to a file

Export Data

Import fields from a file into this form

Import Data

Clear all of the fields on this form

Reset Form

Lock the fields on this form to prevent changes

Lock Supplier Fields

## RoHS Material Composition Declaration

Declaration Type \*

Simplified

**RoHS Directive 2002/95/EC** **RoHS Definition:** Quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material for Cadmium

Supplier certifies that it gathered the information it provides in this form concerning RoHS restrictive substances using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

RoHS Declaration \*

3 - Item(s) does not contain RoHS restricted substances per the definition above except for lead in solders and selected exemptions, if any

Supplier Acceptance \*

Accepted

**Exemptions:** If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.

Exemption List Version

EL-2006/690/EC

+ - 7a. Lead in high melting temperature type solders (i.e. lead based solder alloys containing 85% by weight or more lead).

## Declaration Signature

**Instructions:** Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.

Supplier Digital Signature

## Homogeneous Material Composition Declaration for Electronic Products

**SubItem Instructions:** The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

**Substance Instructions:** [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

**Line Functions:** +I Inserts a New Item /SubItem +M Inserts a new Material +C Inserts a new Substance Category +S Inserts a new Substance - Deletes the element line

		Item/SubItem Name		Homogeneous Material		Weight	Unit of Measure	Level		Substance Category	Substance		CAS	Exempt	Weight	Unit of Measure	Tolerance		PPM			
																	-	+				
+I	-I	7BVT*A16C8HC		+M	-M	Silicon Die	7.288249	mg	+C	-C	Supplier	Silicon die	+S	-S	Silicium (Si)	7440-21-3		6.617	mg			907,94
									+C	-C	Supplier	Die metallization	+S	-S	Nichel (Ni)	7440-02-0		0.619	mg			84,870
													+S	-S	(Gold (Au))	7440-57-5		0.052	mg			7,182
		+M	-M	Leadframe		1,688.17	mg	+C	-C	Supplier	Alloy		+S	-S	Copper (Cu)	7440-50-8		1,685.979	mg			998,70
													+S	-S	Iron (Fe)	7439-89-6		0.777	mg			460
													+S	-S	Iron Phosphide (FeP)	26508-33-8		1.418	mg			840
		+M	-M	Leadframe coating		4.431	mg	+C	-C	Supplier	Coating		+S	-S	Nickel (Ni)	7440-02-0		4.431	mg			1,000,0
		+M	-M	Die Attach		21.52707	mg	+C	-C	A	Lead/Lead Compound		+S	-S	Lead (Pb)	7439-92-1	7a. Lead	19.864	mg			922,78
									+C	-C	Supplier	Soft solder	+S	-S	Silver (Ag)	7440-22-4		1.045	mg			48,524
													+S	-S	Tin (Sn)	7440-31-5		0.554	mg			25,738
								+C	-C	B	Antimony/Antimony C		+S	-S	Antimony (Sb)	7440-36-0		0.064	mg			2,951
		+M	-M	Subelement		89.2	mg	+C	-C	Supplier	Ceramic		+S	-S	Nickel (Ni)	7440-02-0		1.07	mg			12,000
													+S	-S	Phosphorus (P)	12185-10-3		0.08	mg			900
													+S	-S	Manganese (Mn)	7439-96-5		3.479	mg			39,000
													+S	-S	Titanium (Ti)	7440-32-6		0.366	mg			4,100
													+S	-S	Molybdenum oxide	1313-27-5		4.46	mg			50,000
													+S	-S	Alumina (Al2O3)	1344-28-1		79.745	mg			894,00
		+M	-M	Encapsulation		320.3598	mg	+C	-C	B	Antimony/Antimony C		+S	-S	Antimony Trioxide	1333-86-4		9.611	mg			30,000
								+C	-C	Supplier	Moulding Compound		+S	-S	Silica, vitreous	60676-86-0		232.261	mg			725,00
													+S	-S	Quartz	14808-60-7		1.602	mg			5,000
													+S	-S	Phenol resin	9003-35-4		28.832	mg			90,000
													+S	-S	Carbon Black	1333-86-4		1.602	mg			5,000
													+S	-S	Epoxy Cresol Novolak	29690-82-2		40.045	mg			125,00

						+C	-C	B	Brominated Flame Ret	+S	-S	Brominated Epoxy Resin	68928-70-1		6.407	mg			20,000
+M	-M	Finishing	9.02	mg	+C	-C	Supplier		Connection coating	+S	-S	Tin (Sn)	7440-31-5		9.02	mg			1,000,0