



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D
<i>* : Required Field</i>			

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2018-06-15
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Contact Phone *	Refer to Supplier Comment section	Contact Email *	Refer to Supplier Comment section
Authorized Representative *	Rossana Bonaccorso	Representative Title	ADG MD CHAMPION
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement			
Supplier Acceptance *	true	Legal Declaration *	Standard

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STPS5L60SF	HA7R*Z72Q85U	A	Z6IA	2018-06-15
	Amount	UoM	Unit type	ST ECOPACK Grade
	91.1	mg	Each	ECOPACK® 2
	Comment	ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant (in each organic material)		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
1	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
Not Applicable	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
QFF	6.5 - 4.6 - 1.1	3	flat	
Comment	Package: PSMC-3L-EP			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-April 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : ELV directive : 2000/53/EC amended 2016/774 _May 2016	
Query	Response
1 - Product(s) meets EU ELV requirements without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
Exemption Id.	Description
8e	Lead in high melting temperature type solders (i.e. lead-based alloys containing 85 % by weight or more lead)

QueryList : California Prop65 list, dated 15th December 2017			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	0.04	Die	417
Lead	0.07	Soft solder	779

QueryList : REACH-15th January 2018				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	HA7R*Z7ZQ85U					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	M-011 Other inorganic materials	2.699	mg	supplier	die	Silicon (Si)	7440-21-3		2.444	mg	905588	26828
				supplier	metallization	Aluminium (Al)	7429-90-5		0.142	mg	52616	1559
				supplier	passivation	Nickel (Ni)	7440-02-0		0.015	mg	5558	165
				supplier	metallization	Titanium (Ti)	7440-32-6		0.003	mg	1112	33
				supplier	metallization	Tungsten (W)	7440-33-7		0.005	mg	1852	55
				supplier	Passivation	Silicon Oxide	7631-86-9		0.021	mg	7781	231
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.002	mg	741	23
				supplier	back side metallization	Gold (Au)	7440-57-5		0.005	mg	1853	55
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.023	mg	8522	252
				supplier	polymer die coating	Durimide	Proprietary		0.039	mg	14377	426
Lead frame	Copper & its alloys	37.091	mg	supplier	alloy	Copper (Cu)	7440-50-8		35.997	mg	970505	395137
				supplier	alloy	Phosphorus (P)	7723-14-0		0.056	mg	1510	615
				supplier	alloy	Iron (Fe)	7439-89-6		0.964	mg	25990	10582
				supplier	alloy	Zinc(Zn)	7440-66-6		0.074	mg	1995	812
Soft solder	Solder	0.084	mg	supplier	solder	Tin (Sn)	7440-31-5		0.004	mg	47619	44
				JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high me	0.071	mg	845238	779
				supplier	solder	Silver (Ag)	7440-22-4		0.002	mg	23810	22
				supplier	solder	Polyglycol ether	9038-95-3		0.007	mg	83333	77
Clips	Copper & its alloys	8.909	mg	supplier	clips	Copper (Cu)	7440-50-8		8.646	mg	970479	94907
				supplier	clips	Phosphorus (P)	7723-14-0		0.013	mg	1459	143
				supplier	clips	Iron (Fe)	7439-89-6		0.232	mg	26041	2547
				supplier	clips	Zinc(Zn)	7440-66-6		0.018	mg	2021	198
Encapsulation	Other Organic Materials	40.671	mg	supplier	mold compound	Amourphous Silica	60676-86-0		32.537	mg	800005	357157
				supplier	mold compound	Solid Epoxy Resin 1	223769-10-6		2.237	mg	55002	24555
				supplier	mold compound	Solid Epoxy Resin 2	85954-11-6		3.457	mg	84999	37947
				supplier	mold compound	Phenol Resin	205830-20-2		1.424	mg	35013	15631
				supplier	mold compound	Carbon Black	60676-86-0		0.203	mg	4991	2228
				supplier	mold compound	Crystalline Silica	14808-60-7		0.813	mg	19990	8924
Connection coating	Other inorganic materials	1.646	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		1.646	mg	1000000	18068