



## Materials Declaration Form

<b>IPC Form Type *</b>	1752 Distribute	<b>Version</b>	2
<b>Sectionals *</b>	Material Info Manufacturing Info	<b>Subsectionals *</b>	A-D <i>* : Required Field</i>

Supplier Information			
<b>Company Name *</b>	STMicroelectronics	<b>Response Date *</b>	2018-09-24
<b>Company Unique ID</b>	NL 008751171B01		
<b>Contact Name *</b>	Refer to Supplier Comment section		Refer to Supplier Comment section
<b>Contact Phone *</b>	Refer to Supplier Comment section	<b>Contact Email *</b>	Refer to Supplier Comment section
<b>Authorized Representative *</b>	Giovanni Giacopello	<b>Representative Title</b>	ADG MD Champion
<b>Representative Phone *</b>	Refer to Supplier Comment section	<b>Representative Email *</b>	Refer to Supplier Comment section
<b>Supplier Comment</b>	Online Technical Support - STMicroelectronics : <a href="http://www.st.com/web/en/support/support.html">http://www.st.com/web/en/support/support.html</a>		

**Uncertainty Statement**


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement		
<b>Supplier Acceptance *</b>	true	<b>Legal Declaration *</b> Standard

**Legal Statement**

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STW22N95K5	R1LW*VJLLA52	A	3068	2018-09-24
Amount	UoM	Unit type	ST ECOPACK Grade	
4430.00	mg	Each	ECOPACK2	
	Comment	ECOPACK® 2 is STMicroelectronics trade name for ROHS compliant device without Brominated and Chlorinated compound (900ppm) and without Antimony oxide flame retardant ( in each organic material)		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles	 life.augmented	
NA	NA	NA		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NA	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
QFN	15.75-20.15-5.15	3	Through-hole	
Comment	TO 247			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-March 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : ELV directive : 2000/53/EC amended 2017/2096 _November 2017	
Query	Response
1 - Product(s) meets EU ELV requirements without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
Exemption Id.	Description
8e	Lead in high melting temperature type solders (i.e. lead-based alloys containing 85 % by weight or more lead)

QueryList : California Prop65 list, dated 25th May 2018			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	1.07	Die - Leadframe	241
Lead	19.69	Soft solder	4445

QueryList : REACH-27th June 2018				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product
Lead	1000 ppm	19.691	Soft solder	4445
2 - Product(s) does not contain REACH Substances Of Very High Concern in any Embedded article nor Homogeneous Material above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	Amount in Embedded Article / Homogeneous Material (mg)	Application - Article / Homogeneous Material	ppm in Article /Homogeneous Material
Lead	1000 ppm	19.691	Soft solder	954993

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	R1LW*VILA52					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	M-011 Other inorganic materials	23.358	mg	supplier	die	Silicon (Si)	7440-21-3		22.547	mg	965280	5090
				supplier	metallization	Aluminium (Al)	7429-90-5		0.317	mg	13571	73
				supplier	Passivation	Silicon Nitride	12033-89-5		0.106	mg	4538	24
				supplier	Passivation	Silicon Oxide	7631-86-9		0.169	mg	7235	38
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.011	mg	471	2
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.154	mg	6593	35
Leadframe	M-004 Copper and its alloys	2826.183	mg	supplier	alloy	Silver (Ag)	7440-22-4		0.054	mg	2312	12
				supplier	alloy	Copper (Cu)	7440-50-8		2821.521	mg	998350	636912
				supplier	alloy	Iron (Fe)	7439-89-6		2.825	mg	1000	638
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.848	mg	300	191
				supplier	metallization	Nickel (Ni)	7440-02-0		0.915	mg	324	207
				supplier	metallization	Phosphorus (P)	7723-14-0		0.074	mg	26	17
Soft solder	Solder	20.619	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high mel	19.691	mg	954993	4445
				supplier	solder	Silver (Ag)	7440-22-4		0.516	mg	25025	116
				supplier	solder	Tin (Sn)	7440-31-5		0.412	mg	19982	93
				supplier	wire	Aluminium (Al)	7429-90-5		0.160	mg	993789	36
Bonding wires	M-003 Aluminum and its alloys	0.161	mg	supplier	wire	Magnesium (Mg)	7439-95-4		0.001	mg	6211	0
Bonding Ribbons	M-009 Other non-ferrous metals and	2.717	mg	supplier	Ribbon	Aluminium (Al)	7429-90-5		2.717	mg	1000000	613
Encapsulation	M-011 Other inorganic materials	1547.666	mg	supplier	mold compound	Silica, vitreous	60676-86-0		1346.469	mg	870000	303943
				supplier	mold compound	Epoxy resin	25068-38-6		154.767	mg	100000	34936
				supplier	mold compound	Phenol resin	29690-82-2		38.692	mg	25000	8734
				supplier	mold compound	Carbon Black	1333-86-4		7.738	mg	5000	1747
connections coating	Solder	9.296	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		9.296	mg	1000000	2098