



## Materials Declaration Form

<b>IPC Form Type *</b>	1752 Distribute	<b>Version</b>	2
<b>Sectionals *</b>	Material Info Manufacturing Info	<b>Subsectionals *</b>	A-D  * : Required Field

Supplier Information			
<b>Company Name *</b>	STMicroelectronics	<b>Response Date *</b>	2019-02-28
<b>Company Unique ID</b>	NL 008751171801		
<b>Contact Name *</b>	Refer to Supplier Comment section		Refer to Supplier Comment section
<b>Contact Phone *</b>	Refer to Supplier Comment section	<b>Contact Email *</b>	Refer to Supplier Comment section
<b>Authorized Representative *</b>	Rossana Bonaccorso	<b>Representative Title</b>	ADG MD Champion
<b>Representative Phone *</b>	Refer to Supplier Comment section	<b>Representative Email *</b>	Refer to Supplier Comment section
<b>Supplier Comment</b>	Online Technical Support - STMicroelectronics : <a href="http://www.st.com/web/en/support/support.html">http://www.st.com/web/en/support/support.html</a>		

**Uncertainty Statement**

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.


**Legal Statement**

<b>Supplier Acceptance *</b>	true	<b>Legal Declaration *</b>	Standard
------------------------------	------	----------------------------	----------

**Legal Statement**

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STD134N4F7AG	TXDP*OD4QJ52	A	3068	2019-02-28
	Amount	UoM	Unit type	ST ECOPACK Grade
	330.00	mg	Each	ECOPACK1
	Comment	ECOPACK® or ECOPACK® 1 is STMicroelectronics trade name for ROHS compliant devices		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
1	260	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NA	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
SIP	6.5-6.1-2.3	3	GULL WING	
Comment	TO 252 DPAK			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-March 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : ELV directive : 2000/53/EC amended 2017/2096 _November 2017	
Query	Response
1 - Product(s) meets EU ELV requirements without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
Exemption Id.	Description
8e	Lead in high melting temperature type solders (i.e. lead-based alloys containing 85 % by weight or more lead)

QueryList : California Prop65 list, dated 23rd November 2018			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	0.12	Die - Leadframe	367
Lead	4.28	Soft solder	12973
Antimony trioxide	1.89	Mold compound	5727

QueryList : REACH-15th January 2019				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product
Lead	1000 ppm	4.281	Soft solder	12973
2 - Product(s) does not contain REACH Substances Of Very High Concern in any Embedded article nor Homogeneous Material above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	Amount in Embedded Article / Homogeneous Material (mg)	Application - Article / Homogeneous Material	ppm in Article /Homogeneous Material
Lead	1000 ppm	4.281	Soft solder	954941

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	TXDP*OD4QI52					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	M-011 Other inorganic materials	1.351	mg	supplier	die	Silicon (Si)	7440-21-3		1.227	mg	908216	3718
				supplier	metallization	Aluminium (Al)	7429-90-5		0.046	mg	34049	139
				supplier	Passivation	Silicon Nitride	12033-89-5		0.013	mg	9623	39
				supplier	Passivation	Silicon Oxide	7631-86-9		0.020	mg	14804	61
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.002	mg	1480	6
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.029	mg	21466	88
				supplier	back side metallization	Vanadium (V)	7440-62-2		0.002	mg	1480	6
				supplier	back side metallization	Silver (Ag)	7440-22-4		0.012	mg	8882	36
Leadframe	M-004 Copper and its alloys	165.043	mg	supplier	alloy	Copper (Cu)	7440-50-8		164.729	mg	998097	499179
				supplier	alloy	Iron (Fe)	7439-89-6		0.165	mg	1000	500
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		0.050	mg	304	152
				supplier	metallization	Nickel (Ni)	7440-02-0		0.092	mg	557	279
				supplier	metallization	Phosphorus (P)	7723-14-0		0.007	mg	42	22
Soft solder	Solder	4.483	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high mel	4.281	mg	954941	12973
				supplier	solder	Silver (Ag)	7440-22-4		0.112	mg	24983	339
				supplier	solder	Tin (Sn)	7440-31-5		0.090	mg	20076	273
Bonding wires	M-011 Other inorganic materials	1.009	mg	supplier	wire	Aluminium (Al)	7429-90-5		1.005	mg	996036	3045
				supplier	wire	Magnesium (Mg)	7439-95-4		0.004	mg	3964	12
				supplier	mold compound	Silica, vitreous	60676-86-0		126.597	mg	805996	383627
Encapsulation	M-011 Other inorganic materials	157.069	mg	supplier	mold compound	Epoxy Cresol Novolak	29690-82-2		10.995	mg	70001	33318
				supplier	mold compound	Phenol resin	9003-35-4		6.283	mg	40002	19039
				supplier	mold compound	Biphenyl epoxy resin	85954-11-6		9.424	mg	59999	28558
				supplier	mold compound	Antimony Trioxide	1309-64-4		1.885	mg	12001	5712
				supplier	mold compound	Brominated Epoxy Resin	40039-93-8		1.100	mg	7003	3333
				supplier	mold compound	Carbon black	1333-86-4		0.785	mg	4998	2379
Connections coating	Solder	1.045	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		1.045	mg	1000000	3167