



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D

** : Required Field*

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2020-11-05
Company Unique ID	NL 008751171B01		
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Contact Phone *	Refer to Supplier Comment section	Contact Email *	Refer to Supplier Comment section
Authorized Representative *	giovanni giacopello	Representative Title	ADG MD CHAMPION
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.


Legal Statement

Supplier Acceptance *	true	Legal Declaration *	Standard
------------------------------	------	----------------------------	----------

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
VN5050AJTR-E	ARWL*VNL7AEC	A	64BA	2020-11-05
	Amount	UoM	Unit type	ST ECOPACK Grade
	84	mg	Each	ECOPACK 1
Comment	ECOPACK® or ECOPACK® 1 is STMicroelectronics trade name for ROHS compliant devices			

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
3	260	3		
Bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
Not Applicable	Tin (Sn), matte, annealed	Copper Alloy	CD00311182	

Package Designator	Size	Nbr of instances	Shape	
QFP	4.90,3.90,1.55	12	gull wing	
Comment	PowerSSO 12 monoframe. MDF valid for CPs: VN5050AJ-E,VN5050AJTR-E			

QueryList : RoHS Directive 2011/65/EU-July 2011 Annex II amended by Delegated Directive 2015/863-March 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : ELV directive : 2000/53/EC amended 2020/363_ March 2020	
Query	Response
1 - Product(s) meets EU ELV requirements without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
Exemption Id.	Description
8e	Lead in high melting temperature type solders (i.e. lead-based alloys containing 85 % by weight or more lead)

QueryList : California Prop65 list, dated 3rd January 2020			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	0.02	die	238
Lead	1.68	soft solder	19952
Antimony trioxide	0.57	encapsulation	6786

QueryList : REACH-25th June 2020				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product
Lead	1000 ppm	1.68	Soft solder	19952
2 - Product(s) does not contain REACH Substances Of Very High Concern in any Embedded article nor Homogeneous Material above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	Amount in Embedded Article / Homogeneous Material (mg)	Application - Article / Homogeneous Material	ppm in Article /Homogeneous Material
Lead	1000 ppm	1.676	Soft solder	954986

Responsible metals sourcing	
Query	Response
The component is containing at least one of the following metals : Cobalt , Gold , Tantalum , Tin , Tungsten.	true
The following metals are present is the component :	Gold, Tin,
This product is in the scope of the responsible metals sourcing, its compliance is covered by our company processes .	

Material Composition Declaration :						Mfr Item Name	ARWL*VNL7AEC					
note : Substance present with less 0.001mg will not be declared in this document												
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	M-011 Other inorganic materials	3.134	mg	supplier	die	Silicon(Si)	7440-21-3		2.904	mg	926612	34571
				supplier	metallisation	Aluminium(Al)	7429-90-5		0.018	mg	5743	214
				supplier	metallisation	Copper(Cu)	7440-50-8		0.024	mg	7658	286
				supplier	metallisation	Gold(Au)	7440-57-5		0.004	mg	1276	48
				supplier	metallisation	Nicke(Ni)	7440-02-0		0.020	mg	6382	238
				supplier	metallisation	Titanium(Ti)	7440-32-6		0.077	mg	24569	917
				supplier	Passivation	Silicon nitride(SiN)	12033-89-5		0.014	mg	4467	167
				supplier	passivation	Silicon oxide	7631-86-9		0.037	mg	11806	440
				supplier	polymer coating	Polyimide	Proprietary		0.036	mg	11487	429
				supplier	alloy & coating	Copper(Cu)	7440-50-8		29.188	mg	971088	347476
Leadframe	M-004 Copper and its alloys	30.057	mg	supplier	alloy & coating	Iron(Fe)	7439-89-6		0.687	mg	22857	8179
				supplier	alloy & coating	Iron Phosphide(FeP)	26508-33-8		0.041	mg	1364	488
				supplier	alloy & coating	Zinc(Zn)	7440-66-6		0.036	mg	1198	429
				supplier	alloy & coating	Silver (Ag)	7440-22-4		0.105	mg	3493	1250
				supplier	solder	Lead(Pb)	7439-92-1	7a-Lead in high melting temper	1.676	mg	954986	19952
Soft solder	Solder	1.755	mg	supplier	solder	Tin(Sn)	7440-31-5		0.035	mg	19943	417
				supplier	solder	Silver(Ag)	7440-22-4		0.044	mg	25071	524
Bonding wires	M-008 Precious metals	0.104	mg	supplier	wire	Gold(Au)	7440-57-5		0.104	mg	1000000	1238
Bonding wires 2	M-004 Copper and its alloys	0.170	mg	supplier	wire	Copper(Cu)	7440-50-8		0.170	mg	1000000	2024
Encapsulation	M-011 Other inorganic materials	47.785	mg	supplier	mold compound	Silica vitreous	60676-86-0		39.327	mg	822999	468179
				supplier	mold compound	Epoxy Cresol Novolac	29690-82-2		3.345	mg	70001	39821
				supplier	mold compound	Phenol resin	9003-35-4		1.911	mg	39992	22750
				supplier	mold compound	Biphenyl epoxy resin	85954-11-6		1.434	mg	30009	17071
				supplier	mold compound	Antimony trioxide	1309-64-4		0.573	mg	11991	6821
				supplier	mold compound	Brominated epoxy resin	40039-93-8		0.956	mg	20006	11381
				supplier	mold compound	Carbon black	1333-86-4		0.239	mg	5002	2845
connections coating	Solder	0.995	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		0.995	mg	1000000	11845