



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D <i>* : Required Field</i>

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2018-10-08
Company Unique ID	NL 008751171B01		
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Contact Phone *	Refer to Supplier Comment section	Contact Email *	Refer to Supplier Comment section
Authorized Representative *	Giovanni Giacopello	Representative Title	ADG MD Champion
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement		
Supplier Acceptance *	true	Legal Declaration *
		Standard

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
STPS30H60CG-TR	7SD2*Z02S02U	A	3068	2018-10-08
	Amount	UoM	Unit type	ST ECOPACK Grade
	1380.00	mg	Each	ECOPACK1
	Comment	ECOPACK® or ECOPACK® 1 is STMicroelectronics trade name for ROHS compliant devices		

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
1	245	3		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NA	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
SIP	10.2-9.15-4.5	2	gull wing	
Comment	D2PAK			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-March 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : ELV directive : 2000/53/EC amended 2017/2096 _November 2017	
Query	Response
1 - Product(s) meets EU ELV requirements without any exemptions	FALSE
2 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	TRUE
Exemption Id.	Description
8e	Lead in high melting temperature type solders (i.e. lead-based alloys containing 85 % by weight or more lead)

QueryList : California Prop65 list, dated 25th May 2018			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	0.23	Die - Leadframe	169
Lead	12.20	Soft solder	8843
Antimony trioxide	6.74	Encapsulation	4884

QueryList : REACH-27th June 2018				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product
Lead	1000 ppm	12.203	Soft solder	8843
2 - Product(s) does not contain REACH Substances Of Very High Concern in any Embedded article nor Homogeneous Material above the limits per the definition within REACH				FALSE
CategoryLevel_Name	CategoryLevel_Threshold	Amount in Embedded Article / Homogeneous Material (mg)	Application - Article / Homogeneous Material	ppm in Article /Homogeneous Material
Lead	1000 ppm	12.203	Soft solder	954926

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	7SD2*202502U					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	M-011 Other inorganic materials	14.131	mg	supplier	die	Silicon (Si)	7440-21-3		13.746	mg	972755	9961
				supplier	metallization	Aluminium (Al)	7429-90-5		0.085	mg	6015	62
				supplier	metallization	Nickel (Ni)	7440-02-0		0.062	mg	4388	45
				supplier	metallization	Titanium (Ti)	7440-32-6		0.013	mg	921	9
				supplier	metallization	Tungsten (W)	7440-33-7		0.020	mg	1415	14
				supplier	Passivation	Silicon Oxide	7631-86-9		0.084	mg	5944	61
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.007	mg	495	5
				supplier	back side metallization	Gold (Au)	7440-57-5		0.020	mg	1415	14
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.094	mg	6652	68
				Leadframe	M-004 Copper and its alloys	778.633	mg	supplier	alloy	Copper (Cu)	7440-50-8	
supplier	alloy	Iron (Fe)	7439-89-6						0.779	mg	1000	564
supplier	alloy	Iron Phosphide (FeP)	26508-33-8						0.234	mg	301	170
supplier	metallization	Nickel (Ni)	7440-02-0						0.077	mg	99	56
supplier	metallization	Phosphorus (P)	7723-14-0						0.006	mg	8	4
Soft solder	Solder	12.779	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high mel	12.203	mg	954926	8843
				supplier	solder	Silver (Ag)	7440-22-4		0.320	mg	25041	232
				supplier	solder	Tin (Sn)	7440-31-5		0.256	mg	20033	186
Bonding wires	M-003 Aluminum and its alloys	10.288	mg	supplier	wire	Aluminium (Al)	7429-90-5		10.288	mg	1000000	7455
Encapsulation	M-011 Other inorganic materials	561.680	mg	supplier	mold compound	Silica, vitreous	60676-86-0		452.714	mg	806000	328054
				supplier	mold compound	Epoxy Cresol Novolak	29690-82-2		39.318	mg	70001	28491
				supplier	mold compound	Phenol resin	9003-35-4		22.467	mg	40000	16280
				supplier	mold compound	Biphenyl epoxy resin	85954-11-6		33.701	mg	60000	24421
				supplier	mold compound	Antimony Trioxide	1309-64-4		6.740	mg	12000	4884
				supplier	mold compound	Brominated Epoxy Resin	40039-93-8		3.932	mg	7000	2849
				supplier	mold compound	Carbon black	1333-86-4		2.808	mg	4999	2035
connections coating	Solder	2.489	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		2.489	mg	1000000	1804