



Materials Declaration Form

IPC	1752	Version	2
Form Type *	Distribute		
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D * : Required Field

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2020-04-27
Company Unique ID	NL 008751171B01		
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Contact Phone *	Refer to Supplier Comment section	Contact Email *	Refer to Supplier Comment section
Authorized Representative *	Floriana SAN BIAGIO	Representative Title	AMS MD CHAMPION
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement

While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement

Supplier Acceptance *	true	Legal Declaration *	Standard
------------------------------	------	----------------------------	----------

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
	IDO7*1930ASW	A	BO2A	2020-04-27
	Amount	UoM	Unit type	ST ECOPACK Grade
	77	mg	Each	ECOPACK* 3
Comment	ECOPACK® 3 is STMicroelectronics trade name for ROHS compliant device without use of any ROHS exemption and without Halogen nor Antimony			

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
1	260	3		
Bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
Not Applicable	Nickel/Palladium/Gold (Ni/Pd/Au)	Copper Alloy	0	

Package Designator	Size	Nbr of instances	Shape	
DSO	4.9 x 3.9	8	gull wing	
Comment	07 SO 08 .15 JEDEC; MDF is valid for TS3931YDT			

QueryList : RoHS Directive 2011/65/EU-July 2011 – Annex II amended by Directive 2015/863-March 2015	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	TRUE
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	FALSE
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	FALSE
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	FALSE
Exemption Id.	Description

QueryList : ELV directive : 2000/53/EC amended 2020/363_March 2020	
Query	Response
1 - Product(s) meets EU ELV requirements without any exemptions	TRUE
2 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	FALSE
Exemption Id.	Description

QueryList : California Prop65 list, dated 3rd January 2020			
Query			Response
1 - The product does not contain identified substance from California Prop 65 List, no exposure to consumers is foreseen			FALSE
2 - The product is containing below substance(s) from California Prop 65 List, no exposure to consumers is foreseen			TRUE
Substance	amount in product (mg)	Application	ppm in product
Nickel	0.43	alloy	5621

QueryList : REACH-16th January 2020				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				TRUE
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product
,	0			
2 - Product(s) does not contain REACH Substances Of Very High Concern in any Embedded article nor Homogeneous Material above the limits per the definition within REACH				TRUE
CategoryLevel_Name	CategoryLevel_Threshold	Amount in Embedded Article / Homogeneous Material (mg)	Application - Article / Homogeneous Material	ppm in Article /Homogeneous Material
,	0		,	

QueryList : Korea Chemical Control Act_ 27 Dec 2017 update				
Query				Response
The Product does contain at least one of the substances listed in Chemical Control Act				NO
Substance	Homogeneous Material impacted	Content in Homogeneous Material (mg)	Concentration in the material(%)	Application Purpose

Material Composition Declaration : note : Substance present with less 0.001mg will not be declared in this document						Mfr Item Name	IDO7*1930ASW				5000001.0	1000000.0
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	M-011 Other inorganic materials	0.901	mg	supplier	die	Silicon(Si)	7440-21-3		0.879	mg	975583	11490
				supplier	metallisation	Aluminium(Al)	7429-90-5		0.004	mg	4440	52
				supplier	Passivation	Silicon nitride(SiN)	12033-89-5		0.002	mg	2220	26
				supplier	passivation	Silicon oxide	7631-86-9		0.016	mg	17758	209
				supplier	alloy & coating	Copper(Cu)	7440-50-8		27.705	mg	958087	362157
Leadframe	M-004 Copper and its alloys	28.917	mg	supplier	alloy & coating	Nickel(Ni)	7440-02-0		0.430	mg	14870	5621
				supplier	alloy & coating	Iron(Fe)	7439-89-6		0.652	mg	22547	8523
				supplier	alloy & coating	Iron Phosphide(FeP)	26508-33-8		0.039	mg	1349	510
				supplier	alloy & coating	Zinc(Zn)	7440-66-6		0.034	mg	1176	444
				supplier	alloy & coating	Silver (Ag)	7440-22-4		0.015	mg	519	196
				supplier	alloy & coating	Palladium(Pd)	7440-05-3		0.035	mg	1210	458
				supplier	alloy & coating	Gold(Au)	7440-57-5		0.007	mg	242	92
				supplier	alloy & coating	Silver(Ag)	7440-22-4		0.184	mg	876190	2405
Die attach	M-015 Other organic materials	0.210	mg	supplier	glue	Isobornyl methacrylate	7534-94-3		0.011	mg	52381	144
				supplier	glue	Isobornyl acrylate	5888-33-5		0.011	mg	52381	144
				supplier	glue	Methyl acrylate polymer	87320-05-6		0.004	mg	19048	52
Bonding wires	M-004 Copper and its alloys	0.044	mg	supplier	wire	Copper(Cu)	7440-50-8		0.044	mg	1000000	575
Encapsulation	M-011 Other inorganic materials	46.428	mg	supplier	mold compound	Silica vitreous	60676-86-0		40.207	mg	866008	525582
				supplier	mold compound	Epoxy type resin	proprietary		3.482	mg	74998	45516
				supplier	mold compound	Phenol type resin	proprietary		2.321	mg	49991	30340
				supplier	mold compound	Carbon black	1333-86-4		0.232	mg	4997	3033
				supplier	mold compound	Bismuth compound	7440-69-9		0.186	mg	4006	2431